



**NC805C/6**  
1.8m (6ft) Tail Call Lead



**Overview**

A short 1.8m tail call lead for use with C-TEC's Quanteo and 800 Series Call Systems. Allows user to remotely generate Standard calls from armchairs, beds, etc. Comprises a pear-shaped call push, 1.8m (6ft) trailing lead and a 6.35mm remote jack plug. Easily connects to the 6.35mm remote socket on compatible Quanteo and 800 Series call points. Activating the pear push or removing the tail call lead from a call point's remote socket will generate a Standard call.

**NC805C/14**  
4.2m (14ft) Tail Call Lead



**Overview**

A long 4.2m tail call lead for use with C-TEC's Quanteo and 800 Series Call Systems. Allows user to remotely generate Standard calls from armchairs, beds, etc. Comprises a pear-shaped call push, 4.2m (14ft) trailing lead and a 6.35mm remote jack plug. Easily connects to the 6.35mm remote socket on compatible Quanteo and 800 Series call points. Activating the pear push or removing the tail call lead from a call point's remote socket will generate a Standard call.

**NC805D**  
1.2-3.6m (4-12ft) Coiled Tail Call Lead



**Overview**

An extendable coiled tail call lead for use with C-TEC's Quanteo and 800 Series Call Systems. Allows user to remotely generate Standard calls from armchairs, beds, etc. Comprises a pear-shaped call push, coiled 1.2-3.6m trailing lead and a 6.5mm remote jack plug. Easily connects to the 6.35mm remote socket on compatible Quanteo and 800 Series call points. Activating the pear push or removing the tail call lead from a call point's remote socket will generate a Standard call.

**NC805P**  
Hand/Foot Operated Pneumatic Pad



**Overview**

Ideal for people who find it difficult to press the buttons on standard tail call leads. Must be used in conjunction with a separately available NC805AS Air Switch. Applying pressure to the pneumatic pad operates the highly-sensitive NC805AS air switch which in turn, when connected to a compatible call point's remote socket via its 6.35mm remote jack, triggers a Standard call.

**NC805AS**  
Air Switch for NC805P



**Overview**

Designed for use with C-TEC's NC805P Pneumatic Pad. Applying pressure to the NC805P operates the air switch which in turn triggers a Standard call when the 6.35mm jack plug on the NC805AS is connected to a compatible call point's remote socket. Operates at a minimum differential air pressure of 0.9 p.s.i. (pounds per square inch) or 6220 Pa (pascals) ± 10% at 18°C.

**NC805MD**  
Portable Movement Detector




**Overview**

A simple to operate weight sensor designed to sit under the leg of a bed. Triggers a Standard call when the bed is vacated to alert staff to the prospect of a wandering patient. Portable, robust and easy to adjust. Ideal for use in residential care facilities where it can be used for new patients finding it difficult to adjust or for patients suffering from dementia, etc. Requires no components in the bed itself allowing patients to enjoy a relaxed night's sleep without the fear of triggering an unnecessary call. Easily connects to the 6.35mm remote socket on compatible Quanteo and 800 Series call points.

## QT644

### Floor Pressure Mat



### Overview

A durable 90cm x 60cm (3ft x 2ft) floor pressure mat c/w 2m lead and 6.35mm jack plug.

Designed to trigger a Standard call on a Quantec or 800 Series Call System when foot pressure is detected.

Typically located alongside a bed to alert staff to the prospect of a wandering patient in nursing homes, etc. Can also be used in low-level access control applications.

Tough, durable grey PVC finish with a non-slip rubber base.

Simple and reliable operation

Easily connects to the 6.35mm remote socket on compatible Quantec and 800 Series call points.

For more information on these products, please contact us:



T: 00353 47 86274 / 00353 47 86663

E: [Sales@irishsafetysystems.ie](mailto:Sales@irishsafetysystems.ie)